



Main

Range	Odace
Product or component type	Trailing lead
Aesthetic name	Odace extend
Control type	Mains switch
Number of power socket outlets	3 square
Integrated connection type	2 USB port 5 V DC, maximum load current: 2.4 A
Cable length	1.5 M
Colour tint	White/Aluminium bronze

Complementary

[Ue] rated operational voltage	250 V
[In] rated current	16 A
Outlet poles configuration	2P + E
Outlet standard	French
Socket additional information	Shuttered
Maximum switching capacity	16 A
Pilot light	ON indicator
Material	PC PP (polypropylene)
Length	254 Mm
Width	57 Mm
Depth	40.5 Mm
Quantity per set	Set of 1
Type of packing	Blister

Offer Sustainability

EU RoHS Directive	Pro-active compliance (Product out of EU RoHS legal scope) EU RoHS Declaration
Toxic heavy metal free	Yes
Mercury free	Yes
RoHS exemption information	Yes
China RoHS Regulation	China RoHS Declaration

The information provided in this documentation contains general descriptions and/or technical characteristics of the performance of the products contained herein. This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications. It is the duty of any such user or integrator to perform the appropriate and complete risk analysis, evaluation and testing of the products with respect to the relevant specific application or use thereof. Neither Schneider Electric Industries SAS nor any of its affiliates or subsidiaries shall be responsible or liable for misuse of the information contained herein.

Environmental Disclosure

[Product Environmental Profile](#)

Circularity Profile

[End Of Life Information](#)

Product Life Status : **Commercialised**
