



## Main

Range	Odace
Product or component type	Trailing lead
Aesthetic name	Odace extend
Control type	Mains switch
Number of power socket outlets	5 square
Integrated connection type	2 USB port 5 V DC, maximum load current: 2.4 A
Cable length	1.5 M
Colour tint	Anthracite

## Complementary

[Ue] rated operational voltage	250 V
[In] rated current	16 A
Outlet poles configuration	2P + E
Outlet standard	French
Socket additional information	Shuttered
Maximum switching capacity	16 A
Pilot light	ON indicator
Material	PP (polypropylene)
Length	339 Mm
Width	57 Mm
Depth	40.5 Mm
Quantity per set	Set of 1
Type of packing	Blister

## Offer Sustainability

EU RoHS Directive	Pro-active compliance (Product out of EU RoHS legal scope) <a href="#">EU RoHS Declaration</a>
Toxic heavy metal free	Yes
Mercury free	Yes
RoHS exemption information	<a href="#">Yes</a>
China RoHS Regulation	<a href="#">China RoHS Declaration</a>
Environmental Disclosure	<a href="#">Product Environmental Profile</a>
Circularity Profile	<a href="#">End Of Life Information</a>

Product Life Status : **Commercialised**