



Main

Range	Odace
Product or component type	Trailing lead
Aesthetic name	Odace extend
Control type	Mains switch
Number of power socket outlets	5 square
Integrated connection type	2 USB port 5 V DC, maximum load current: 2.4 A
Cable length	1.5 M
Colour tint	White

Complementary

[Ue] rated operational voltage	250 V
[In] rated current	16 A
Outlet poles configuration	2P + E
Outlet standard	French
Socket additional information	Shuttered
Maximum switching capacity	16 A
Pilot light	ON indicator
Material	PP (polypropylene)
Length	339 Mm
Width	57 Mm
Depth	40.5 Mm
Quantity per set	Set of 1
Type of packing	Blister

Offer Sustainability

EU RoHS Directive	Pro-active compliance (Product out of EU RoHS legal scope) EU RoHS Declaration
Toxic heavy metal free	Yes
Mercury free	Yes
RoHS exemption information	Yes
China RoHS Regulation	China RoHS Declaration
Environmental Disclosure	Product Environmental Profile
Circularity Profile	End Of Life Information

Product Life Status : **Commercialised**