

Product data sheet

Characteristics

T40BG125BDDP12S6

SZ0 FVNR COMBO 1 SC DEV FLA 0.6

Price*: 2894.00 USD

Commercial status

This Product is Obsolete :

 This Product is Obsolete

Main

| | |
|---------------------------------|--|
| Product or component type | Self-protected combination motor controller |
| Range of product | TeSys N Self-Protected Combination Motor Controller |
| Product certifications | CSA UL listed |
| Control circuit | Separate control circuit |
| Provided equipment | Current limiter |
| Phase | 3 phases |
| System Voltage | 600 V AC |
| [Uc] control circuit voltage | 24 V DC |
| Communication port protocol | DeviceNet |
| NEMA degree of protection | NEMA 1 |
| Enclosure material | Painted sheet steel |
| Enclosure type | Standard size |
| Enclosure accessory description | With external reset |
| Auxiliary contact composition | 1 NO + 1 NC |
| NEMA size | 0 |
| Motor power hp | 3 hp 230 V AC 5 hp 460 V AC 5 hp 575 V AC 3 hp 200 V AC |
| Poles description | 3P |
| Local signalling | Red/Green indicator on/off LED |
| Control type | No control units |
| Motor starter type | Non reversing |
| Electrical connection | Screw-clamp terminals |
| Thermal overload type | Solid state advanced class 20 0.15...0.6 A |
| Disconnecter device type | Self-protected combination controller 18 A |

Ordering and shipping details

| | |
|-----------------------|--|
| Category | 21219 - ENCLOSED TESYS N COMB STR SIZE 1 |
| Discount Schedule | CP1 |
| Nbr. of units in pkg. | 1 |
| Package weight(Lbs) | 24.620000000000001 |
| Returnability | N |

Contractual warranty

| | |
|-----------------|-----------|
| Warranty period | 18 months |
|-----------------|-----------|

Product Life Status : **End of commercialisation**