

# Product data sheet

## Characteristics

# T40CA121BDJCP1S6

## SZ1 FVNR COMBO 12/3R SC ASI FLA 8-27

Price\*: 3166.00 USD

### Commercial status

This Product is Obsolete :

 This Product is Obsolete

### Main

Product or component type	Self-protected combination motor controller
Range of product	TeSys N Self-Protected Combination Motor Controller
Product certifications	CSA UL listed
Control circuit	Separate control circuit
Provided equipment	Current limiter
Phase	3 phases
System Voltage	600 V AC
[Uc] control circuit voltage	24 V DC
Communication port protocol	AS-Interface
NEMA degree of protection	NEMA 12/3R
Enclosure material	Painted sheet steel
Enclosure type	Standard size
Enclosure accessory description	With external reset
Auxiliary contact composition	1 NO + 1 NC
NEMA size	1
Motor power hp	10 hp 460 V AC 10 hp 575 V AC 7.5 hp 230 V AC 7.5 hp 200 V AC
Poles description	3P
Local signalling	Red indicator on LED
Control type	Selector switch HAND-OFF-AUTO
Motor starter type	Non reversing
Electrical connection	Screw-clamp terminals
Thermal overload type	Solid state advanced class 20 8...32 A
Disconnecter device type	Self-protected combination controller 27 A

### Ordering and shipping details

Category	21219 - ENCLOSED TESYS N COMB STR SIZE 1
Discount Schedule	CP1
Nbr. of units in pkg.	1
Package weight(Lbs)	24.620000000000001
Returnability	N

### Contractual warranty

Warranty period	18 months
-----------------	-----------

Product Life Status : **End of commercialisation**