

Main

Range of product	Modicon M171/M172
Product or component type	Display module
Supply	External source

Complementary

Display type	LCD display Colour touchscreen
Display resolution	320 x 240 pixels
Colour	White
[Us] rated supply voltage	24 V AC/DC
Power consumption in W	1.3 W 3.2 VA
Overvoltage category	II
Product compatibility	Logic controller M172 Logic controller M171
Height	96 mm
Width	134 mm
Depth	35 mm
Product weight	0.175 kg

Environment

Directives	2011/65/EU - RoHS directive 1907/2006/EC - REACH directive 2014/30/EU - electromagnetic compatibility
Standards	EN 60730-1 EN 60730-2-9 IEC 61000-4-11 IEC 61000-4-2 IEC 61000-4-3 IEC 61000-4-4 IEC 61000-4-5 IEC 61000-4-6 UL 60730-1 UL 60730-2-9 CSA E60730-2-9 CAN/CSA-E60730-1
Product certifications	CE CSA CURus RCM EAC
Ambient air temperature for operation	-20...60 °C
Ambient air temperature for storage	-30...60 °C

IP degree of protection	IP65 on front panel
Pollution degree	2

Offer Sustainability

RoHS (date code: YYWW)	Compliant Schneider Electric Declaration Of Conformity
REACH	Reference not containing SVHC above the threshold

Product Life Status :	Commercialised
-----------------------	-----------------------