

Product data sheet

Characteristics

TVS2EMA16SIC

Surge Protect - EMA - 160kA - 208Y/120VAC - 3P4W - T4X - SW - counter - CSA



by Schneider Electric

Price*: 7949.00 USD

Commercial status

This Product is Obsolete :

This Product is Obsolete

Main

Product or component type	Surge protection device
Range of product	SurgeLogic
Device short name	EMA

Complementary

Surge current	160 kA per phase
System Voltage	208Y/120 V AC
Phase	3 phases
Wiring configuration	4-wire
[Uc] maximum continuous operating voltage	150 V
Nominal discharge current	20 kA
Short-circuit protection	200 kA
Local signalling	Status LED, green = normal operation per phase Status LED, red = fault per phase
Provided equipment	Surge counter Switch-disconnector with integrated switch for off/on/automatic Alarm enable/disable switch
Mounting location	Service entrance
Device mounting	Surface Flush

Environment

NEMA degree of protection	NEMA 4X
Enclosure material	Stainless steel
Standards	ANSI/IEEE C62.41 ANSI/IEEE C62.45 UL Category Section 37.3 UL 1283 ed. 5 UL 1449 ed. 4

Ordering and shipping details

Category	08464 - SURGE PROTECTION EMA
Discount Schedule	DE1B
GTIN	00785901634454
Nbr. of units in pkg.	1
Package weight(Lbs)	37.60000000000001
Returnability	N
Country of origin	US

Product Life Status : **End of commercialisation**