

# Product data sheet

## Characteristics

# TVS2EMA24SI

Surge Protect - EMA - 240kA - 208Y/120VAC -  
3P4W - T4X - SW - CSA



by Schneider Electric

Price\*: 9938.00 USD

### Commercial status

This Product is Obsolete :

This Product is Obsolete

### Main

Product or component type	Surge protection device
Range of product	SurgeLogic
Device short name	EMA

### Complementary

Surge current	240 kA per phase
System Voltage	208Y/120 V AC
Phase	3 phases
Wiring configuration	4-wire
[Uc] maximum continuous operating voltage	150 V
Nominal discharge current	20 kA
Short-circuit protection	200 kA
Local signalling	Status LED, green = normal operation per phase Status LED, red = fault per phase
Provided equipment	Switch-disconnector with integrated switch for off/on/automatic Alarm enable/disable switch
Mounting location	Service entrance
Device mounting	Surface Flush

### Environment

NEMA degree of protection	NEMA 4X
Enclosure material	Stainless steel
Standards	ANSI/IEEE C62.41 ANSI/IEEE C62.45 UL Category Section 37.3 UL 1283 ed. 5 UL 1449 ed. 4

### Ordering and shipping details

Category	08464 - SURGE PROTECTION EMA
Discount Schedule	DE1B
GTIN	00785901653639
Nbr. of units in pkg.	1
Package weight(Lbs)	37.700000000000003
Returnability	N
Country of origin	MX

Contractual warranty

---

Warranty period	18 months
-----------------	-----------

---

Product Life Status : End of commercialisation