



Main

Range	TeSys
Product name	TeSys VARIO
Device short name	VCF
Product or component type	Enclosed emergency stop switch disconnecter
Performance level	High performance
Poles description	3P
Control type	Rotary handle
Handle colour	Red
Handle front plate colour	Yellow
Rotary handle padlocking	1 to 3 padlocks 4...8 mm

Complementary



Marking	0 - 1
[Ue] rated operational voltage	690 V AC
[Uimp] rated impulse withstand voltage	8 KV
[Ithe] conventional enclosed thermal current	10 A
[Ie] rated operational current	8.1 A (AC-23A) at 400 V
Rated operational power in W	4 KW at 400 V (AC-23) 3 KW at 400 V (AC-3)
Intermittent duty class	30
Making capacity	120 A at 400 V AC-21A 120 A at 400 V AC-22A 120 A at 400 V AC-23A
[Icm] rated short-circuit making capacity	1 KA at 400 V at Ipeak
[Icw] rated short-time withstand current	300 A at 400 V duration: 1 s
Rated conditional short-circuit current	10 KA at 400 V - associated fuse 12 A aM 10 KA at 400 V - associated fuse 12 A gG
Breaking capacity	120 A at 400 V (AC-21A) 120 A at 400 V (AC-22A) 120 A at 400 V (AC-23A)
Mechanical durability	100000 Cycles
Electrical durability	100000 Cycles AC-21 30000 Cycles DC-1...5
Environmental characteristic	Standard environment
Suitability for isolation	Yes
Connections - terminals	Power circuit: screw clamp terminals 2.5...4 mm ² - flexible - with cable end Protective earth: screw clamp terminals 2.5...4 mm ² - flexible - with cable end Shield cable earth: cable clips
Tightening torque	2.1 N.M - on screw clamp terminals
Fire resistance	960 °C conforming to IEC 60595-2-1

Base dimension	60 x 60 mm
Height	146 Mm
Width	90 Mm
Depth	131 Mm
Net weight	0.5 Kg

Environment

Standards	IEC 60947-4-1 IEC 60204
Protective treatment	TC
IP degree of protection	IP65 conforming to IEC 60529
Mechanical robustness	Vibrations 10...150 Hz (1 gn) conforming to IEC 60068-2-6 Shocks 11 ms (30 Gn) conforming to IEC 60068-2-27
Ambient air temperature for operation	-20...50 °C

Offer Sustainability

EU RoHS Directive	Under investigation
Toxic heavy metal free	Yes
Mercury free	Yes
RoHS exemption information	 Yes
China RoHS Regulation	 China RoHS Declaration

Contractual warranty

Warranty	18 months
----------	-----------

Product Life Status : **Commercialised**