



Main

Range	Actassi
Product or component type	Empty sliding 19" data panel
Device presentation	Basic
Colour	Dark grey RAL 7016
Additional information	Automatic grounding

Complementary

Type of footprint	Slim
Communication network category	6 6_A 5e
Provided equipment	2 quick fix 19" mountings
Number of rack unit	1U
Cover type	Screened
Number of port	24 FTP/STP
Mounting support	19" rack
Material	PA66 GF20 PA6 DC01 1.2 mm
Height	47 mm
Width	490 mm
Depth	230 mm
Product weight	2.2 kg
Targeted region	Europe Asia Pacific

Environment

Ambient air temperature for operation	-10...55 °C
Standards	IEC 60297 NF C 20-150 ISO/IEC 11801:ed. 2.2, 2011

The information provided in this documentation contains general descriptions and/or technical characteristics of the performance of the products contained herein. This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications. It is the duty of any such user or integrator to perform the appropriate and complete risk analysis, evaluation and testing of the products with respect to the relevant specific application or use thereof. Neither Schneider Electric Industries SAS nor any of its affiliates or subsidiaries shall be responsible or liable for misuse of the information contained herein.

Offer Sustainability

Sustainable offer status	Green Premium product
RoHS (date code: YYWW)	Compliant - since 0935 - Schneider Electric declaration of conformity Schneider Electric declaration of conformity
REACH	Reference not containing SVHC above the threshold
Product environmental profile	Available Product Environmental Profile
Product end of life instructions	Need no specific recycling operations

Contractual warranty

Warranty period	18 months
-----------------	-----------

Product Life Status : **Commercialised**