



Main

Range	Exxact
Product or component type	Switch
Device application	Control
Quantity per set	Set of 5

Complementary

Device mounting	Flush
Device presentation	Complete product
Switch function	1-pole 2-way
Switch pattern	[6/1]
Rated current	16 A at 250 V AC
Colour tint	White (RAL 9003)
Connections - terminals	Screwless terminals
Number of loop terminals	2
Clamping connection capacity	1 x 1.5...2 x 2.5 mm ² for solid cable(s) 1 x 1.5...2 x 2.5 mm ² for solid stranded cable(s)
Material	ABS (acrylonitrile butadiene-styrene)
Fixing mode	By screw: rocker By screw: insert
Embedding depth	15 Mm
Height	87 Mm
Width	87 Mm
Projecting depth	18 Mm

Environment

Standards	EN 60669-1
Product certifications	FIMKO SEMKO CE NEMKO
IP degree of protection	IP44

The information provided in this documentation contains general descriptions and/or technical characteristics of the products contained herein. This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications. It is the duty of any such user or integrator to perform the appropriate and complete risk analysis, evaluation and testing of the products with respect to the relevant specific application or use thereof. Neither Schneider Electric Industries SAS nor any of its affiliates or subsidiaries shall be responsible or liable for misuse of the information contained herein.

Offer Sustainability

REACH Regulation	REACH Declaration
REACH free of SVHC	Yes
EU RoHS Directive	Compliant EU RoHS Declaration
Toxic heavy metal free	Yes
Mercury free	Yes
RoHS exemption information	Yes
China RoHS Regulation	China RoHS Declaration
WEEE	The product must be disposed on European Union markets following specific waste collection and never end up in rubbish bins

Product Life Status : **Commercialised**