



### Main

Range of product	Exxact
Product or component type	Single socket-outlet with residual current device
Number of poles	2
Outlet standard description	With earthing contact
Quantity per set	1 piece

### Complementary

Wiring device mounting	Flush
Rated current	16 A at 230 V AC
Colour tint	White
Connections - terminals	Screwless terminals
Clamping connection capacity	1 x 1.5...2 x 2.5 mm <sup>2</sup> for solid cable(s) 1 x 1.5...2 x 2.5 mm <sup>2</sup> for solid stranded cable(s)
Earth leakage current	30 MA
Earth-leakage protection class	Class A
Material	PC + ASA
Embedding depth	32 Mm
Height	71 Mm
Width	71 Mm
Projecting depth	35 Mm
Product compatibility	To be completed with Exxact frame

### Environment

Standards	IEC 60884-1 SS 4280834 DIN VDE 0620-1 SFS 5610:2004 EN 61008
Product certifications	CE NEMKO SEMKO FIMKO
IP degree of protection	IP20 also with visual parts removed

## Offer Sustainability

Sustainable offer status	Green Premium product
REACH Regulation	<a href="#">REACH Declaration</a>
REACH free of SVHC	Yes
EU RoHS Directive	Compliant <a href="#">EU RoHS Declaration</a>
Toxic heavy metal free	Yes
Mercury free	Yes
RoHS exemption information	<a href="#">Yes</a>
China RoHS Regulation	<a href="#">China RoHS Declaration</a>
Environmental Disclosure	<a href="#">Product Environmental Profile</a>
Circularity Profile	No need of specific recycling operations
WEEE	The product must be disposed on European Union markets following specific waste collection and never end up in rubbish bins

## Contractual warranty

Warranty	18 months
----------	-----------

Product Life Status : **Commercialised**