



Main

Product brand	Schneider Electric
Range compatibility	Wiser
Range	Exxact
Product or component type	Electronic switch

Complementary

Device presentation	Insert with central cover plate
Dimmer control	Toggle on/off
Product compatibility	To be completed with Exxact frame
Load type	Incandescent lamp: 2200 W at 230 V AC Halogen lamp: 2000 W at 230 V AC Motor (single-phase): 1000 VA at 230 V AC LV halogen lamps: 1050 VA at 12 V AC (electronic transformer) LV halogen lamps: 500 VA at 12 V AC (wound transformer) LED lamp: 100 W at 230 V AC Compact fluorescent lamp: 100 W at 230 V AC
[Ue] rated operational voltage	230 V AC 50/60 Hz
Rated current	10 A 140 μ F 10 AX cos phi = 0.6
Associated fuse rating	16 A
Colour tint	White (RAL 9003)
Surface finish	Glossy
Number of FUNCTION keys	2
Local signalling	Programmable: 1 LED (green/red)
Signalling function	Light ON when switch is actuated Locator Programming indication
Number of outputs	1
Control type	Rocker Remote control by auxiliary push-button Remote control Wiser App
Software name	Wiser App: management of the pulse generator Wiser App: upgrade device firmware Wiser App: define LED status Wiser App: random function Wiser App: astro function Wiser App: weekday switching Wiser App: program the switching time Wiser App: enable timer mode/overtravel time Wiser App: management of trigger settings Wiser App: enable timer with pre-warning
Time delay range	1 s...24 h (overtravel)
Maximum number of connected devices	Bluetooth: <15 (smart device) Bluetooth: <10 (Wiser device) Bluetooth: <10 (multiway switching between coupled device)

Communication network type	Wireless (2.4 GHz), 2.5 mW
System requirements	Android 5.1 or higher Wiser App Apple iOS 10.3 or higher Wiser App Bluetooth 4.1 or higher Bluetooth Wiser Home Touch Wiser Home control
Connected auxiliaries	Unlimited number of push-buttons, distance : 100 m
Provided equipment	Centre plate User manual
Wiring configuration	With neutral
Connections - terminals	Screw terminal
Number of loop terminals	2
Clamping connection capacity	1.5...2.5 mm ² for solid cable(s) 1.5...2.5 mm ² for solid stranded cable(s)
Shape of screw head	Pozidriv No 1 and combi
Tightening torque	0.5 N.M
Material	PC (polycarbonate) GF10 FR: casing Metal: terminals ABS (acrylonitrile butadiene-styrene): central plate
Mounting support	Wall
Device mounting	Flush
Fixing mode	By screws and clamp
Type of installation	Indoor installation
Type of packing	Carton
Embedding depth	33 Mm
Depth	43 Mm
Width	71 Mm
Height	71 Mm
Standards	EN 60730-2-7 EN 60669-2-1 EN 300-328 EN 301-489-17
Directives	2014/30/EU - electromagnetic compatibility 2014/35/EU - low voltage directive
Product certifications	NF VDE NEMKO CE FIMKO SEMKO EAC

Environment

Ambient air temperature for operation	5...40 °C
Ambient air temperature for storage	5...40 °C
IP degree of protection	IP20 IP21 with marking on visual parts

Offer Sustainability

EU RoHS Directive	Compliant EU RoHS Declaration
Mercury free	Yes
RoHS exemption information	Yes
China RoHS Regulation	China RoHS Declaration
Environmental Disclosure	Product Environmental Profile
Circularity Profile	End Of Life Information
WEEE	The product must be disposed on European Union markets following specific waste collection and never end up in rubbish bins

Product Life Status : **Commercialised**