



Main

Range of product	Easy Harmony XA2
Product or component type	Complete illuminated push-button
Device short name	XA2
Bezel material	Plastic
Mounting diameter	22 Mm

Complementary

Sale per indivisible quantity	1
Protective treatment	TC
Operating position	Any position
Fixing center	>= 30 x 40 mm (panel) - thickness: 1...5 mm
Fixing mode	Fixing nut recommended torque: 2,2 N.m (Us +/- 10 %)
Shape of signaling unit head	Round
Type of operator	Spring return
Operator profile	White flush
Contacts type and composition	1 NO
Contact operation	Slow-break
Mechanical durability	1500000 Cycles
Connections - terminals	Screw clamp terminals, clamping capacity: 2 x 1.5 mm ² Screw clamp terminals, clamping capacity: 1 x 2.5 mm ² Faston terminals, connection size: 6.3 mm Screw clamp terminals, clamping capacity: 1 x 0.5 mm ²
Tightening torque	0,8 N.M
Short-circuit protection	10 A gL fuse conforming to IEC 60269-1
[Ith] conventional free air thermal current	10 A
[Ui] rated insulation voltage	600 V conforming to IEC 60947-4-1
[Uimp] rated impulse withstand voltage	6 KV conforming to IEC 60947-1
[Ie] rated operational current	0,27 A at 250 V, DC-13, Q600 3 A at 240 V, AC-15, A600
Electrical durability	500000 Cycles, DC-13, 0,2 A at 110 V, operating rate <60 cyc/mn, load factor: 0,5 conforming to IEC 60947-5-1 500000 Cycles, DC-13, 3 A at 230 V, operating rate <60 cyc/mn, load factor: 0,5 conforming to IEC 60947-5-1
Signalling type	Steady
Light source	LED
Bulb base	BA 9s
[Us] rated supply voltage	220 V AC 50/60 Hz
Supply voltage limits	176...242 V AC

Current consumption	< 20 mA
Service life	10000 H
Width	30 Mm
Height	42 Mm
Depth	79,5 Mm
Net weight	0,064 Kg

Environment

Ambient air temperature for storage	-40...70 °C
Ambient air temperature for operation	-25...55 °C
Overvoltage category	Class I conforming to IEC 536
IP degree of protection	IP65
IK degree of protection	IK03 conforming to IEC 60529
Standards	GB 14048.1 GB 14048.5 IEC 60947-5-1 IEC 60947-1
Product certifications	CE CCC
Vibration resistance	10 gn (f= 40...500 Hz) conforming to IEC 60068-2-6
Shock resistance	70 gn (duration = 11 ms) for half sine wave acceleration conforming to IEC 60068-2-27

Đơn vị đóng gói

Loại đơn vị của Gói hàng 1	PCE
Số lượng Đơn vị trong Gói hàng 1	1
Trọng lượng Gói hàng 1	62 G
Chiều cao Gói hàng 1	3 Cm
Chiều rộng Gói hàng 1	4 Cm
Chiều dài Gói hàng 1	9 Cm
Loại đơn vị của Gói hàng 2	S02
Số lượng Đơn vị trong Gói hàng 2	70
Trọng lượng Gói hàng 2	4,599 Kg
Chiều cao Gói hàng 2	15 Cm
Chiều rộng Gói hàng 2	30 Cm
Chiều dài Gói hàng 2	40 Cm
Loại đơn vị của Gói hàng 3	P06
Số lượng Đơn vị trong Gói hàng 3	1120
Trọng lượng Gói hàng 3	81,584 Kg
Chiều cao Gói hàng 3	75 Cm
Chiều rộng Gói hàng 3	80 Cm
Chiều dài Gói hàng 3	60 Cm

Offer Sustainability

Sustainable offer status	Green Premium product
REACH Regulation	REACH Declaration
EU RoHS Directive	Pro-active compliance (Product out of EU RoHS legal scope) EU RoHS Declaration
Mercury free	Yes
RoHS exemption information	Yes
China RoHS Regulation	China RoHS Declaration
Environmental Disclosure	Product Environmental Profile
Circularity Profile	End Of Life Information
WEEE	The product must be disposed on European Union markets following specific waste collection and

Product Life Status : **Commercialised**