



Commercial status

This Product is Obsolete :

 This Product is Obsolete

Main

Range of product	Harmony XAP
Product or component type	Die-cast empty control station
Device short name	XAPG
Product destination	For Ø 22 mm control and signalling units
Product front plate size	80 x 80 mm
Usable depth	2.93 In (74.5 mm)
Number of cut-out	2 cut-outs
Colour of base of enclosure	Grey RAL 7032)
Colour of cover	Grey RAL 7032)
Material	Zinc alloy
Cable entry	1 hole with blanking plug for cable gland 0.55 in (14 mm) 1 hole without blanking plug for cable gland 0.55 in (14 mm)
Product mounting	Flush mounting
IP degree of protection	IP65 IEC 60529 IP657 NF C 20-010

Complementary

Number of vertical rows	2
Net Weight	1.32 Lb(US) (0.6 kg)

Environment

Protective treatment	TC
Ambient air temperature for storage	-40...158 °F (-40...70 °C)
Ambient air temperature for operation	-13...158 °F (-25...70 °C)
Electrical shock protection class	Class I IEC 60536 Class I NF C 20-030

Ordering and shipping details

Category	18406-WORLD SERVICE PARTS(OTHER OP INT)
Discount Schedule	CS2
GTIN	03389118115774
Package weight(Lbs)	1.60 Lb(US) (0.724 kg)
Returnability	No

Packing Units

Package 1 Height	0.950 Dm
Package 1 width	0.850 Dm
Package 1 Length	0.900 Dm

Offer Sustainability

Sustainable offer status	Green Premium product
REACH free of SVHC	Yes
EU RoHS Directive	Pro-active compliance (Product out of EU RoHS legal scope) EU RoHS Declaration
Toxic heavy metal free	Yes
Mercury free	Yes
RoHS exemption information	Yes
China RoHS Regulation	China RoHS Declaration
Environmental Disclosure	Product Environmental Profile
Circularity Profile	End Of Life Information

Contractual warranty

Warranty	18 months
----------	-----------

Product Life Status : **End of commercialisation**

XAPG1502 may be replaced by any of the following products:



662

Metal control stations for 22 mm metal push buttons (XB4/ZB4 range)

Reason for Substitution: End of life | Substitution date: 30 Apr 2020 |