

XE2NP3168

1 CO - 1 NO - 1 NC MBB GOLD FLASHED CONNECTOR

Product availability: Non-Stock - Not normally stocked in distribution facility

Price*: 73.00 USD



Main

Range of product	OsiSense XC
Series name	Standard format
Product or component type	Limit switch contact block
Device short name	XE2N
Associated body	ZCT26
Number of poles	2
Contacts type and composition	1 NO + 1 NC
Contact operation	Slow-break, make before break

Complementary

Product compatibility	XCKT
Electrical connection	Screw-clamp terminals 1 x 0.5...2 x 2.5 mm ²
Contacts insulation form	Zb
Contacts material	Gold flashed contacts
Positive opening	With
Minimum actuation speed	6 M/Min
Contact code designation	A300, AC-15 (U _e = 240 V), I _e = 3 A 10 A EN/IEC 60947-5-1 appendix A Q300, DC-13 (U _e = 250 V), I _e = 0.27 A EN/IEC 60947-5-1 appendix A
Maximum resistance across terminals	25 MOhm IEC 60255-7 category 3
[U _i] rated insulation voltage	300 VUL 508 500 V 3) IEC 60947-1 300 VCSA C22.2 No 14
[U _{imp}] rated impulse withstand voltage	6 KV IEC 60664 6 KV IEC 60947-1
Short-circuit protection	10 A cartridge fuse gG
Electrical durability	5000000 Cycles, DC-13 120 V, 7 W 60 cyc/mn 0.5 IEC 60947-5-1 appendix C 5000000 Cycles, DC-13 24 V, 13 W 60 cyc/mn 0.5 IEC 60947-5-1 appendix C 5000000 Cycles, DC-13 48 V, 9 W 60 cyc/mn 0.5 IEC 60947-5-1 appendix C

Ordering and shipping details

Category	22449 - LIMIT SWITCHES,ACCESSORIES
Discount Schedule	T
GTIN	03389110196856
Nbr. of units in pkg.	1
Package weight(Lbs)	0.05 Lb(US) (0.02 kg)
Returnability	No
Country of origin	ID

Packing Units

Package 1 Height	1.100 Dm
Package 1 width	0.250 Dm
Package 1 Length	0.750 Dm

Contractual warranty

Warranty	18 months
----------	-----------

Product Life Status : **Commercialised**