



Trạng thái thương mại

Ngày bán : THG 1 23, 2021

⚠ Ngày bán

Main

Range of product	Telemecanique Inductive proximity sensors XS
Series name	General purpose
Sensor type	Inductive proximity sensor
Product specific application	-
Sensor name	XSD
Sensor design	Form 80 x 80 x 40
Size	40 mm
Body type	Fixed
Enclosure material	Plastic
Type of output signal	Discrete
Wiring technique	2-wire
[Sn] nominal sensing distance	50 Mm
Discrete output function	1 NO + 1 NC
Electrical connection	Screw-clamp terminals
[Us] rated supply voltage	12...240 V AC/DC
IP degree of protection	IP67

Complementary

Detection face	Frontal
Detector flush mounting acceptance	Flush mountable
Material	Plastic
Front material	Plastic
Output circuit type	AC/DC
Cable entry	1 entry tapped for Pg 13.5 cable gland
Switching capacity in mA	5...100 mA DC 5...500 mA AC
Switching frequency	<= 10 Hz
Marking	CE
Depth	40 Mm
Height	100 Mm
Width	80 Mm

The information provided in this documentation contains general descriptions and/or technical characteristics of the products of the products contained herein. This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications. It is the duty of any such user or integrator to perform the appropriate and complete risk analysis, evaluation and testing of the products with respect to the relevant specific application or use thereof. Neither Schneider Electric Industries SAS nor any of its affiliates or subsidiaries shall be responsible or liable for misuse of the information contained herein.

Environment

Product certifications	CCC
Ambient air temperature for operation	-25...70 °C

Đơn vị đóng gói

Loại đơn vị của Gói hàng 1	PCE
Số lượng Đơn vị trong Gói hàng 1	1
Trọng lượng Gói hàng 1	536 G
Chiều cao Gói hàng 1	5,4 Cm
Chiều rộng Gói hàng 1	9 Cm
Chiều dài Gói hàng 1	15 Cm
Loại đơn vị của Gói hàng 2	S02
Số lượng Đơn vị trong Gói hàng 2	11
Trọng lượng Gói hàng 2	6,234 Kg
Chiều cao Gói hàng 2	15 Cm
Chiều rộng Gói hàng 2	30 Cm
Chiều dài Gói hàng 2	40 Cm

Offer Sustainability

Sustainable offer status	Green Premium product
EU RoHS Directive	Pro-active compliance (Product out of EU RoHS legal scope) EU RoHS Declaration
Mercury free	Yes
RoHS exemption information	Yes
Environmental Disclosure	Product Environmental Profile

Contractual warranty

Warranty	18 months
----------	-----------

Product Life Status : **End of commerc. - Block**