

Product data sheet

Characteristics

XZCPV12V2L2

pre-wired connectors XZ - elbowed female - M12 -
3 wires - cable 2m

Product availability: Stock - Normally stocked in distribution facility

Price*: 15.00 USD



Main

Accessory / separate part category	Cabling accessory
Accessory / separate part type	Pre-wired connectors
Series name	General purpose

Complementary

Electrical connection	M12, 3 pins elbowed female connector
Cable connector fixing	Screw-on
Collar material	Metal
Status LED	Without
Cable length	6.56 ft (2 m)
Cable outer diameter	0.2 in (5.2 mm)
Cable composition	3 x 0.34 mm ²
Wire insulation material	PVC
System Voltage	60 V AC 75 V DC
Line Rated Current	3 A
Contact resistance	5000 µOhm
Insulating resistance	1 GΩ
Product weight	0.16 lb(US) (0.074 kg)

Environment

IP degree of protection	IP67 IP65
Product certifications	CULus
Ambient air temperature for operation	-13...176 °F (-25...80 °C) (static)
Ambient air temperature for storage	-13...176 °F (-25...80 °C)

Ordering and shipping details

Category	22483 - MACHINE CABLES
Discount Schedule	DS3
GTIN	00785901963530
Nbr. of units in pkg.	1
Package weight(Lbs)	0.90000000000000002
Returnability	Y
Country of origin	CZ

Product Life Status : **Commercialised**