

# Product data sheet

## Characteristics

# ZC2JE643

limit switch head ZC2J - side steel roller plunger  
horizontal - corrosive

Price\*: 256.00 USD



## Commercial status

This Product is Obsolete :

 This Product is Obsolete

## Main

Range of product	OsiSense XC
Series name	Special format
Product or component type	Limit switch head
Device short name	ZC2J
Head type	Plunger head
Product compatibility	XC2J
Movement of operating head	Linear
Type of operator	Side roller plunger spring return metal with horizontal roller)
Type of approach	Lateral approach, 2 directions

## Complementary

Switch actuation	By 30° cam
Positive opening	Without
Net Weight	0.46 Lb(US) (0.21 kg)
Head material	Metal

## Environment

Ambient air temperature for operation	-13...158 °F (-25...70 °C)
Ambient air temperature for storage	-40...158 °F (-40...70 °C)
Environmental characteristic	Corrosive

## Ordering and shipping details

Category	18407-WORLD SERVICE PARTS(SENSORS)
Discount Schedule	T
GTIN	03389118131507
Package weight(Lbs)	0.54 Lb(US) (0.245 kg)
Returnability	No

Packing Units

Package 1 Height	0.010 Dm
Package 1 width	0.010 Dm
Package 1 Length	0.020 Dm

Contractual warranty

Warranty	18 months
----------	-----------

Product Life Status : **End of commercialisation**