

“BME NOP 0300(C) IEC61850 CONFIGURATOR” RELEASE HISTORY

Version #	Date of Publication	Internal reference	Description
V3.2 IR03	05/2020	PEP0539778R	The duration is long when saving BMENOP IEDCT project files
<p>Filename: IEC61850CT_SV3.2_INSTALLER.7z SHA256: D11896B7A9D75B516AD3EBAC9B98B6DFDD25E0F2F40A527207902B216E932573</p>			

“BME NOP 0300(C) IEC61850 CONFIGURATOR” RELEASE HISTORY

Version #	Date of Publication	Internal reference	Description
V3.1	01/2020		Updated MongoDB Version
		PEP0451131R	Add a filter option in I/O mapping table for selecting all specific data attribute (e.g. "q"/"t", etc.)
		PEP0459064R	BMENOP0300(C) can synchronize its local time (e.g. time source came from external NTP server, NOP act as NTP Client) to M580 CPU via X-bus
		PEP0446596R PEP0518466R	"Error – Object reference not set to an instance of an object" message after importing some 3rd party CID/SCD/ICD files when click "SAVE" for IEDCT
		PEP0467474R	The initial value of DO in parallel with Beh would not take effect when mapping DO - Beh (Data attribute) in the I/O mapping table.
		PEP0381240R	IEC61850 Control command won't take effect after downloading an IEC61850 project file which I/O mapping is mismatch with Data Model.
		PEP0544836R	some items cannot be selected due to lack of scroll bar after multiple IP address configured in IEDCT ACL table
		PEP0557988R	Select more devices and specific device cannot be selected when .SCD file imported in Server page of IEDCT
		PEP0554472R	GOOSE subscribing not updating new values from IED
		PEP0570497R	IED communication timeout optimization
Filename: IEC61850CT_SV3.1_INSTALLER.7z SHA256: 2876F0B7A6DBDE0F256628CB9C005600202A20752101EF44A8FE5587EF1A7A29			