

Basic Rack PDU


Overview

The APC by Schneider Electric Basic Rack PDU distributes power to devices in the rack.

Outlets. The Rack PDU has twenty-four NEMA 5-20 outlets.

Power cord. The 10-foot (3.05-meter) power cord terminates with a NEMA L5-30 connector.

AP7532



Electrical

Input connector	NEMA L5-30 plug
Output connectors	24-NEMA 5-20 outlets
Nominal input voltage	120 VAC
Acceptable input voltage	± 10% of normal voltage
Input frequency	50/60 Hz
Physical	
Size (H × W × D)	63.75 x 2.19 x 1.73 in (161.92 x 5.56 x 4.39 cm)
Shipping Dimensions (H × W × D)	84.00 x 6.00 x 5.00 in (213.36 x 15.24 x 12.7 cm)
Weight	12.25 lb (5.56 kg)
Shipping weight	14.25 lb (6.46 kg)
Environmental	
Elevation (above MSL)	
Operating Storage	0-15,000 ft (0-4500 m) 0-50,000 ft (0-15 000 m)
Temperature Operating Storage	23 to 115° F (–5 to 45° C) –13 to 149° F (–25 to 65° C)
Humidity Operating Storage	5–95% RH non-condensing 5–95% RH non-condensing
Compliance	
Safety verification	cULus

You can find customer support and warranty information on the APC website, **www.apc.com**.

© 2021 APC by Schneider Electric. All rights reserved.

990-1893B