

APC AP8866/AP8887 Plug Information



The AP8866/AP8887 uses an IEC309 pin and sleeve type splashproof (IP 44), interlocking connector; there are a wide-variety of connector form-factors for user power connectivity.

Male Plug on the AP8866/AP8887

Type	North America IEC 309, 60A
Format	Standard Splashproof IP44
Wires	4, 3P+G
Voltage AC	3Ø250
Clock Position of Ground	9



Splashproof plugs best interconnect with splashproof connectors; however, the plugs fit watertight connectors without the ability to utilize the threaded locking feature.

Splashproof Connectors

					
Manufacturer ↓	Standard	Economical	Straight	Angled 15°	Angled 80°
Walther Electric	361409	360409	460409	560409	564409

Watertight Connectors

Compatible, but will not be watertight

				
Manufacturer ↓	Standard	Straight	Angled 15°	Angled 80°
Walther Electric	369409	469409	569409	568409
Cooper	CH460C9W	CH460R9W	CH460R	
Hubbell	HBL460C9W	HBL460R9W		
RusselStoll	RS460C9W	RS460R9W		