

Panel Thickness	Number		
E dim.	of		
inches (mm)	Gasket		
1/16 (1.6)	4		
1/8 (3.2)	3		
3/16 (4.8)	2		
1/4 (6.4)	1		





A dim. inches (mm)					
Depressed (Stop)	Midway (Neutral)	Extended (Start)			
0.50 (12.6)	-	0.81 (20.6)			

Note: - Drawings Not To Scale - Drawings Subject to Change Without Notice - Dimensions are inches next to [Millimeters]			Part No.: 9001KR9P1		Schneic <i>V</i> Elec
	CSA File: CE Marked: RoHS: NEMA / IP Rating: Key Number: Key Removal: Light Module Supply Voltage:	E78403 CCN Nk LR24590 Class 3 Yes NEMA 1/2/3/3R/- n/a n/a 110/120VACat50 Transformer 1	3211-03 4/6/12/13 Water tight, Dust tight and Oil tight (Indoor/Outdoor), IP66	Description: Ring Nut Material: Operator Type: Operator Action: Button Type: Guard Type: Button/Cap Color: Lens Type: Lens Color: Knob Type: Knob Color: Number of Positions:	Specification: 30mm Push Button Chromium Plated Zinc Illuminated Maintained (Push/Pull) Screw-On Mushroom Operator (mushroon No Guard No Button not applicable not applicable not applicable n/a 2



Schneider Electric United States North American Division Boston One Campus 800 Federal Street Andover, MA 01810, USA Phone:+1 8773425173 Email: CCC@us.schneider-electric.com

oom head not included)