



Note:

- Drawings Not To Scale
- Drawings Subject to Change Without Notice
- Dimensions are inches next to [Millimeters]

Part No.:

9080LBA262101



by **Schneider Electric**

Schneider Electric United States
 North American Division
 Boston One Campus
 800 Federal Street
 Andover, MA 01810, USA
 Phone: +1 8773425173
 Email: CCC@us.schneider-electric.com

Technical Information:

For Use With: Copper or Aluminum Wire
 Terminal Type: Lugs
 Cover: 9080LB22
 Service Class: C
 UL File: E60616 XCFR2
 CSA File: 70361 6228-01
 RoHS: Yes
 CE Marked: Yes
 Flammability Rating: UL94V-0
 35mm Track Adapter: N/A

Description:

Ampere Rating:
 Max. Voltage Rating:
 Number of Poles:
 Wire Range - Main:
 Wire Range - Branch:
 Short Circuit Current Ratings with Circuit Breakers:
 Short Circuit Current Ratings with Fuses:

Specification:

175A/135A (Cu/Al)
 600V AC/DC
 2
 (1)#14 to #2/0 AWG
 (1)#14 to #2/0 AWG
 N/A
 Up to 65kA