



Note:

- Drawings Not To Scale
- Drawings Subject to Change Without Notice
- Dimensions are inches next to [Millimeters]

Part No.:

9080LBA265112



by **Schneider Electric**

Schneider Electric United States
 North American Division
 Boston One Campus
 800 Federal Street
 Andover, MA 01810, USA
 Phone: +1 8773425173
 Email: CCC@us.schneider-electric.com

Technical Information:

For Use With:	Copper or Aluminum Wire
Terminal Type:	Lugs
Cover:	9080LB52
Service Class:	C
UL File:	E60616 XCFR2
CSA File:	70361 6228-01
RoHS:	Yes
CE Marked:	Yes
Flammability Rating:	UL94V-0
35mm Track Adapter:	N/A

Description:	
Ampere Rating:	380A/310A (Cu/Al)
Max. Voltage Rating:	600V AC/DC
Number of Poles:	2
Wire Range - Main:	(1)#4 to 500 AWG/kcmil
Wire Range - Branch:	(12)#14 to #2 AWG
Short Circuit Current Ratings with Circuit Breakers:	Up to 65 kA
Short Circuit Current Ratings with Fuses:	Up to 100kA

Specification: