


**Note:**

- Drawings Not To Scale
- Drawings Subject to Change Without Notice
- Dimensions are inches next to [Millimeters]

Part No.:

**ZB6ZB15B**



Schneider Electric United States  
 North American Division  
 Boston One Campus  
 800 Federal Street  
 Andover, MA 01810, USA  
 Phone: +1 8773425173  
 Email: CCC@us.schneider-electric.com

**Technical Information:**

UL File: E164353 CCN NKCR  
 CSA File: LR44087 Class 321103  
 CE Marked: Yes  
 RoHS: Yes  
 NEMA / IP Rating: NEMA 1/2/3/4/4X/12, IP65  
 Terminal Type: Quick Connect/Solder Tabs

**Specification:**

Description:  
 Head Type: not applicable  
 Style: Protected LED 12/24V  
 Bezel Material:  
 Color: White  
 Operator Action: n/a  
 Operator Type: Illuminated