





KNOCKOUTS					
SYMBOL	A	B	C	D	E
IN	.50	.75	1.00	1.25	1.50
MM	13	19	25	32	38



DUAL DIMENSIONS: INCHES
MILLIMETERS

CATALOG NUMBER	MAXIMUM SYSTEM VOLTAGE	MAINS AMPERE RATING	SPACES	MAXIMUM NUMBER OF SINGLE POLE CIRCUITS	MAIN WIRE SIZE AWG AL/CU
Q06-12L100F/S	120/240VAC 1Ø 3W	100	6	12	# 8-1
Q06-12L100DF/S			6	12	
Q06-12L100DFCU/SCU			6	12	
Q08-16L100F/S			8	16	
Q08-16L100DF/S			8	16	
Q08-16L100DFCU/SCU			8	16	

NOTES:
FINISH - GRAY BAKED ENAMEL ELECTRODEPOSITED OVER CLEANED PHOSPHATIZED STEEL.
UL LISTED - FILE E-6294
NEUTRALS - INSULATED GROUNDABLE.

Q0 LOAD CENTERS
GENERAL PURPOSE NEMA TYPE 1 ENCLOSURE - INDOOR



DWG. NO. 3019