



KNOCKOUTS		
SYMBOL	IN	MM
A	.50	13
B	.75	19
C	1.00	25

DUAL DIMENSIONS, INCHES  
MILLIMETERS

CATALOG NUMBER	MAXIMUM SYSTEM VOLTAGE	MAINS AMPERE RATING	SPACES	MAXIMUM NUMBER OF SINGLE-POLE CIRCUITS	MAIN WIRE SIZE AWG	NEUTRAL/EQUIPMENT GROUND TERMINALS (G EACH)
Q02-4L60NRNM+	120/240 VAC 1Ø 3W	60 ●	2	4	#14-#4 AL/CU	#14-#4 AL/CU

- NOTES:  
 UL LISTED  
 SUITABLE FOR USE AS SERVICE EQUIPMENT.  
 + WHEN MOUNTING, ALLOW 1.50IN / 38MM CLEARANCE ON HINGE SIDE FOR DOOR TO OPEN.  
 ● SUITABLE FOR USE ON SYSTEMS WITH UP TO 10K RMS SYMMETRICAL AMPERES AVAILABLE FAULT CURRENT AT 240VAC.

Q0 LOAD CENTERS  
 RAINPROOF NEMA TYPE 3R ENCLOSURE - OUTDOOR  
 NON-METALLIC

**SQUARE D COMPANY**

DWG. NO. 3106