



Note:

Drawings Not To Scale
Drawings Subject to Change Without Notice
Dimensions are inches next to [Millimeters]

Part No.:

ATS01N106FT

Schneider Electric United States
North American Division
Boston One Campus
800 Federal Street
Andover, MA 01810, USA
Phone:+1 8773425173
Email: CCC@us.schneider-electric.com

Technical Information:

Control Voltage: Weight [lb]/[kg]: UL File No.: CSA File: 0.35/0.16 E184727 224330

Other:

IEC/EN 60947-4-2 CE,UL,CSA,C-Tick and CCC

Specification:

Constant & Variable Torque

Description:
Family:
Product Line:
Application:
Output Ampere Rating:
hp rating 110V Single Phase: 1/4 hp
hp rating 208V Single Phase: 1/2
kW rating 230V Single Phase: 0.75 kW
hp rating 230V Single Phase: 1/2
kW rating 230V three Phase: 1/2
kW rating 230V three Phase: .75 - 1.1 kW
hp rating 230V three Phase: 1-1.5 hp
kW Rating 400V three phase: 2.2 kW
hp rating 460V three phase: 2 - 3 hp
Enclosure Rating:

Enclosure Rating: IP20