



Note:
 - Drawings Not To Scale
 - Drawings Subject to Change Without Notice
 - Dimensions are inches next to [Millimeters]

Part No.:
BMXEHC0200

Schneider Electric
 Schneider Electric United States
 North American Division
 Boston One Campus
 800 Federal Street
 Andover, MA 01810, USA
 Phone: +1 8773425173
 Email: CCC@us.schneider-electric.com

Technical Information:

Mounting:	Any slot except 0
UL & CSA:	Yes
CE:	Yes
RoHS:	Yes
Class 1 Div 2 CSA:	Yes
GOST/BV/GL/RMRS/ABS:	Yes
Weight [kg]:	0.112

Specification:

Description:	
Selection:	M340 PAC
Conf.Coating - 25C to 70C op.temp.:	No
No. Channels:	2
Max Frequency:	60 KHZ
Number of Inputs:	6
Number of Outputs:	2
Connection Type:	BMXXTSHSC20