

MAXIMUM POWER RATINGS FOR 1PH AND 3PH MOTORS  
50/60 HZ AC3 DUTY


	SINGLE PHASE		THREE PHASE			
	115V	230V	200V	230V	460V	575V
D40	3 HP	5 HP	10 HP	10 HP	30 HP	30 HP
D50	3 HP	7.5 HP	10 HP	15 HP	40 HP	40 HP
D65	5 HP	10 HP	20 HP	20 HP	50 HP	50 HP

AUXILIARY CONTACTS

CODE (1)	NO	NC
11	1	1

COIL VOLTAGES FOR LC1 D09 TO D80

VOLTS	50 HZ CODE (2)	60 HZ CODE (2)	50/60 HZ CODE (2)
24	B5	B6	B7
110	F5	F6	F7
120	-	G6	-
127	G5	-	-
208	-	L6	-
220	M5	M6	M7
240	U5	U6	U7
277	-	W6	-
380	Q5	Q6	Q7
415	N5	-	N7
440	R5	R6	R7
480	-	T6	-
575	-	S6	-
600	-	X6	-
660	Y5	-	-



DEPTH: 4.49

Catalog Number: LC1 D40(1)(2), LC1 D50(1)(2), LC1 D65(1)(2)  
 Ratings: LC1 D40 - 600V/40A, LC1 D50 - 600V/50A, LC1 D65 - 600V/85A  
 UL File/CCN: E48539/MLDX  
 CSA File/Class: LR43304/3211 04  
 Meets Standards: IEC 158-1, IEC 947-1, IEC 947-4  
 Weight: 1.15kg  
 Wire Size: Power #3-#10 / Control #10-#18  
 Terminal torque: 35 LB-IN  
 Mounting Hwd.: 35mm DIN rail, #10 screws

"THE SQUARE D COMPANY HAS PROPRIETARY RIGHTS TO THE INFORMATION CONTAINED HEREON. THIS INFORMATION REMAINS THE PROPERTY OF SQUARE D COMPANY AND MAY BE USED ONLY IN CONFORMANCE WITH INSTRUCTIONS ISSUED BY SQUARE D COMPANY. USER SHOULD VERIFY DRAWINGS ARE TO THE LATEST/CURRENT REVISION PRIOR TO INCORPORATING IN A DESIGN FILE."

**DO NOT SCALE DRAWING**  
UNLESS OTHERWISE SPECIFIED DIMENSIONS ARE IN INCHES

THIRD ANGLE PROJECTION  
TOLERANCES  
UNLESS OTHERWISE SPECIFIED  
2 PLACE DECIMALS ± .01

IEC CONTACTOR  
LC1 D40(1)(2)  
LC1 D50(1)(2)  
LC1 D65(1)(2)

**SQUARE D COMPANY**

DWG# E0200401-01  
NO.