


Note:
 - Drawings Not To Scale
 - Drawings Subject to Change Without Notice
 - Dimensions are inches next to [Millimeters]

Part No.:
HGA361506


by Schneider Electric
 Schneider Electric United States
 North American Division
 Boston One Campus
 800 Federal Street
 Andover, MA 01810, USA
 Phone: +1 8773425173
 Email: CCC@us.schneider-electric.com

Technical Information:

General Application: For Use With: Approvals: Mounting Type: Terminal Type: Wire Size: Weight: Mounting Height:	Provides overload and short circuit protection I-line Panelboards and Switchboards UL Listed - CSA Certified - IEC Rated I-Line Plug-On I-Line Connection (ON end) - Lugs (OFF end) #14-3/0 AWG (Al/Cu) 5 Pounds 4.5 Inches
--	--

Specification:

Description: Number of Poles: Ampere Rating: Voltage Rating: Interrupting Rating: Fixed AC Magnetic Trip: Phase Connection:	PowerPact H-frame Thermal Magnetic Circuit Breaker 3-Pole 150A 600VAC 65kA at 240VAC - 35kA at 480VAC - 18kA at 600VAC Hold: 900A - Trip: 1700A CBA
--	---