


**Note:**

- Drawings Not To Scale
- Drawings Subject to Change Without Notice
- Dimensions are inches next to [Millimeters]

Part No.:

**LC1D25P7**



Schneider Electric United States  
North American Division  
Boston One Campus  
800 Federal Street  
Andover, MA 01810, USA  
Phone: +1 8773425173  
Email: CCC@us.schneider-electric.com

**Technical Information:**

Rating: 600V / 25A  
 UL File/CCN: E164862 / NLDX  
 CSA File: LR43364 3211 04  
 Meets Standards: IEC 60647-4  
 Weight: 0.82 lb (0.37 kg)  
 Termination Method: Screw Clamp  
 Wire Size: Power: #6 - #14 AWG  
 Control: #10 - #18 AWG  
 Terminal torque: Power: 20 lb-in (2.5 Nm)  
 Control: 15 lb-in (1.7 Nm)  
 Mounting Hwd.: 35mm DIN Rail, #8 screw

**Specification:**

Description: TeSys D IEC Contactor - 25A - Vac Coil  
 Type: TeSys D IEC Contactor - 25A - 230Vac Coil  
 Voltages Code: P7 at 230Vac 50/60 Hz

Coil Consumption: Inrush 70 VA  
 Sealed 7.5 VA

Single Phase			Three Phase		
115V	230V	200V	230V	460V	575V
2 HP	3 HP	7.5 HP	7.5 HP	15 HP	20 HP