



**Note:**  
 - Drawings Not To Scale  
 - Drawings Subject to Change Without Notice  
 - Dimensions are inches next to [Millimeters]

Part No.:  
**LC1D65A3P7**

**Schneider Electric**  
 Schneider Electric United States  
 North American Division  
 Boston One Campus  
 800 Federal Street  
 Andover, MA 01810, USA  
 Phone: +1 8773425173  
 Email: CCC@us.schneider-electric.com

**Technical Information:**

Rating: 600V / 65A  
 UL File/CCN: E164862 / NLDX  
 CSA File: LR43364 3211 04  
 Meets Standards: IEC 60647-4  
 Weight: 0.86 lb (0.39 kg)  
 Termination Method: Spring Clamp  
 Wire Size: Power: #2 - #16 AWG  
 Control: #12 - #20 AWG  
 Terminal torque: Power: 70 lb-in (8 Nm)  
 Control: N/A  
 Mounting Hwd.: 35mm DIN Rail, #8 screw

**Specification:**

Description: TeSys D IEC Contactor New Type with Everlink® - 65A - Vac Coil  
 Type: TeSys D IEC Contactor - 65A - 230Vac Coil  
 Voltages Code: P7 at 230Vac 50/60 Hz

Coil Consumption: Inrush 140 VA  
 Sealed 13 VA

Single Phase			Three Phase		
115V	230V	200V	230V	460V	575V
5 HP	10 HP	20 HP	20 HP	40 HP	50 HP