



KNOCKOUTS		
SYMBOL	CONDUIT SIZE	
	IN	MM
A	.50	13
B	.75	19
C	1.00	25
D	1.25	32
E	1.50	38
F	2.00	51
G	2.50	64



DUAL DIMENSIONS: INCHES
MILLIMETERS

CATALOG NUMBER	MAXIMUM SYSTEM VOLTAGE	MAINS AMPERE RATING	SPACES	MAXIMUM NUMBER OF SINGLE POLE CIRCUITS	MAIN WIRE SIZE AWG AL/CU
QO112L200PGRB	120/240VAC 1Ø 3W	200	12	24	#4-250 CU #4-300 AL
QO120M150PRB		150	20	30	
QO120M200PRB		200	20		

NOTES:
 FINISH - GRAY BAKED ENAMEL ELECTRODEPOSITED OVER CLEANED PHOSPHATIZED STEEL.
 UL LISTED - FILE E-6294
 NEUTRALS - INSULATED GROUNDABLE.
 WHEN MOUNTING THESE LOAD CENTERS, ALLOW 1.25/[32] CLEARANCE ON HINGED SIDE FOR THE DOOR TO OPEN.
 LOAD CENTERS WITH "G" IN CATALOG NUMBER INCLUDE A FIELD INSTALLABLE EQUIPMENT GROUND BAR KIT.
 LOAD CENTERS WITH "P" IN CATALOG NUMBER INCLUDE EXTENDED NEUTRALS FOR PLUG ON NEUTRAL READY INTERIORS.

QO LOAD CENTERS
 RAINPROOF NEMA TYPE 3R ENCLOSURES
 SIDE HINGED
 OUTDOOR

SQUARE D[™]
 by Schneider Electric

DWG# PWFDS-SYRS-0212
 NO.