



CATALOG NUMBERS
QON2L40

NOTES:
 INCOMPLETE COMPONENT – THE FINAL ACCEPTANCE OF THIS COMPONENT IS DEPENDANT UPON ITS INSTALLATION AND USE IN COMPLETE EQUIPMENT SUBMITTED TO UL OR CSA.
 UL RECOGNIZED COMPONENT FILE: E6294
 CSA PANELBOARD INTERIOR FILE: LL89066
 SUITABLE FOR USE WITH 75°C COPPER OR ALUMINUM MAIN CONDUCTORS. SEE BRANCH BREAKERS FOR BRANCH WIRE RATINGS.
 USE ONLY SQUARE D TYPE QO, QOA, AND QOC BRANCH CIRCUIT BREAKERS, COMPONENTS, AND ACCESSORIES. USE OF OTHERS VOIDS THE WARRANTY, MAY VOID THE UL LISTING OR CSA CERTIFICATION AND MAY RESULT IN PROPERTY LOSS OR PERSONAL INJURY.
 SHORT CIRCUIT CURRENT RATING
 10,000 RMS SYMMETRICAL AMPERES AT 240VAC MAX. ADDITIONAL OR REPLACEMENT BRANCH CIRCUIT BREAKERS MUST HAVE AN INTERRUPTING RATING EQUAL TO OR GREATER THAN THAT OF THE CIRCUIT BREAKERS WITH THE LOWEST INTERRUPTING RATING PRESENTLY INSTALLED.
 MAXIMUM CONTINUOUS LOADS ON BRANCH CIRCUITS NOT TO EXCEED 80% OF THE RATINGS OF THE CIRCUIT BREAKERS EMPLOYED IN OTHER THAN MOTOR CIRCUITS.

DUAL DIMENSIONS: INCHES
 MILLIMETERS

OEM MOUNTING BASE
 120/240 VAC, 1 PH 3W (WITH NEUTRAL)
 240 VAC, 1 PH, 2W (NEUTRAL NOT USED)
 50 - 60 HERTZ



DWG# QON2L40
 NO.