



Note:
 - Drawings Not To Scale
 - Drawings Subject to Change Without Notice
 - Dimensions are inches next to [Millimeters]

Part No.:
SERM2MMOD485

Schneider Electric
 Schneider Electric United States
 North American Division
 Boston One Campus
 800 Federal Street
 Andover, MA 01810, USA
 Phone: +1 8773425173
 Email: CCC@us.schneider-electric.com

Technical Information:
 GPRS: Class 10 (up to 4Rx 2TX)
 ETSI GSM: Class 4 (2 W at 850/900 MHz), Class 1 (1 W at 1800/1900 MHz)
 Bit Rate: 6.6kbps to 14.4kbps
 SMS: Yes
 Voltage: 5.5 - 32 Vdc
 Current: 350mA

Description: M2M Hardware for M168
PLC Connection: RS485
SIM Reader: 3V - 1.8V

Specification: