



**Note:**

- Drawings Not To Scale
- Drawings Subject to Change Without Notice
- Dimensions are inches next to [Millimeters]

Part No.:

**TM2AMI4LT**

Schneider Electric United States  
 North American Division  
 Boston One Campus  
 800 Federal Street  
 Andover, MA 01810, USA  
 Phone:+1 8773425173  
 Email: CCC@us.schneider-electric.com

**Technical Information:**

Resolution: 12 bits (4096 points)  
 Input Acquisition Period: 160ms/channel (Voltage) 320ms/channel (Temperature)+ 1 controller cycle time  
 Output Transfer Time:  
 Isolation Between Channels and Int. Logic: 2500V AC rms  
 Isolation Between Channels: Non Isolated Between Channels  
 Mounting: 35mm DIN Rail  
 RoHS: Yes  
 Weight [kg]: 0.085

**Specification:**

Description: Analog Input Expansion Module  
 Selection: (0-10V, 0-20mA-Voltage), (Temp probe 2, 3 or 4 Wire Pt100/1000= -200C-600C),(Ni100/1000= -50-100C)  
 Input Range:  
 Output Range:  
 Connection Type: Removable Screw Terminal Block