



Note:
 - Drawings Not To Scale
 - Drawings Subject to Change Without Notice
 - Dimensions are inches next to [Millimeters]

Part No.:
XPSAV11113

Schneider Electric
 Schneider Electric United States
 North American Division
 Boston One Campus
 800 Federal Street
 Andover, MA 01810, USA
 Phone: +1 8773425173
 Email: CCC@us.schneider-electric.com

UL File/CCN: E164353 / NKCR
 CSA File/Class: LR44087 / 3211 03
 CE: Yes
 RoHS: Yes

Technical Information:

Description:
 Voltage: 24 VDC
 Terminal Type: Screw
 Terminal Block: Fixed
 Safety Contacts - Standard: 3
 Safety Contacts - Time Delay: 3
 Auxiliary Contacts:
 Solid State Outputs: 3
 Timing Range: 0 - 300s

Specification: