


**Note:**  
 - Drawings Not To Scale  
 - Drawings Subject to Change Without Notice  
 - Dimensions are inches next to [Millimeters]

Part No.:

**ZB4BD3**



Schneider Electric United States  
 North American Division  
 Boston One Campus  
 800 Federal Street  
 Andover, MA 01810, USA  
 Phone: +1 8773425173  
 Email: CCC@us.schneider-electric.com

**Technical Information:**

UL Listed: Yes  
 UL File: E164353 CCN NKCR  
 CSA Approval: Yes  
 CSA File: LR44087 Class 3211 03  
 CE: Yes  
 RoHS: Yes  
 Bezel Material: Chromed Zinc  
 NEMA / IP Rating: NEMA 1/2/3/4/4X/13; IP66  
 Key Number: n/a  
 Key Removal: n/a  
 Max. # of Contact Blocks: 6  
 Button Marking: none

**Specification:**

Description: 22mm 2 Pos Selector Switch  
 Operator Type: Non-Illuminated  
 Operator Action: Maintained  
 Button Type: Standard Handle  
 Bezel Type: Metal  
 Color: Black  
 Head Type: Round