


Note:
 - Drawings Not To Scale
 - Drawings Subject to Change Without Notice
 - Dimensions are inches next to [Millimeters]

Part No.:

ZB4BG7



Schneider Electric United States
 North American Division
 Boston One Campus
 800 Federal Street
 Andover, MA 01810, USA
 Phone: +1 8773425173
 Email: CCC@us.schneider-electric.com

Technical Information:

UL Listed:	Yes
UL File:	E164353 CCN NKCR
CSA Approval:	Yes
CSA File:	LR44087 Class 3211 03
CE:	Yes
RoHS:	Yes
Bezel Material:	Chromed Zinc
NEMA / IP Rating:	NEMA 1/2/3/4/4X/13; IP66
Key Number:	Ronis 455
Key Removal:	center
Max. # of Contact Blocks:	6
Button Marking:	none

Specification:

Description:	22mm 3 Pos Key Selector
Operator Type:	Non-Illuminated
Operator Action:	sp ret both to C
Button Type:	n/a
Bezel Type:	Metal
Color:	Black
Head Type:	Round