

5. AS A GENERAL GUIDE, THE MINIMUM CLEARANCE REQUIRED FROM ANY OBSTRUCTION IS 6 FEET.
4. PROVIDE A CLEAR VERTICAL EXHAUST FIELD. REVIEW MANUAL FOR DETAILED INSTALLATION
3. MAXIMUM INTAKE AIR TEMPERATURE IS 120°F. INTAKE AIR IS DRAWN IN FROM SIDES AND REAR OF UNIT.
2. ALL DIMENSIONS ARE APPROX. IN INCHES [mm]
1. WEIGHT: 3000 LBS APPROX [1361 Kg]



PERMANENT LOAD BANK - TWO BAY UNIT  
GENERAL REFERENCE OUTLINE DRAWING


Model 4820

1 OF 2


Rev. F

WHEN METERING OPTION SUPPLIED,  
CURRENT TRANSFORMERS MOUNTED  
THIS SIDE. THESE CAN BE FIELD  
RELOCATED TO OTHER SIDE.

RECOMMENDED CONDUIT ENTRY  
AREA FOR CONTROL/BLOWER  
AND LOAD CONNECTIONS



VIEW A-A



GROUND BUS BAR DETAIL  
GROUND BUS BARS IN EACH BAY  
GROUND BUS BARS ARE  
0.25 [6.35] THICK COPPER



PERMANENT LOAD BANK - TWO BAY UNIT  
GENERAL REFERENCE OUTLINE DRAWING

Model 4820 2 OF 2 Rev. F