

5. AS A GENERAL GUIDE, THE MINIMUM CLEARANCE REQUIRED FROM ANY OBSTRUCTION IS 6 FEET.
4. PROVIDE A CLEAR VERTICAL EXHAUST FIELD. REVIEW MANUAL FOR DETAILED INSTALLATION AND SITE CONDITIONS.
3. MAXIMUM INTAKE AIR TEMPERATURE IS 120°F. INTAKE AIR IS DRAWN IN FROM SIDES, END AND BOTTOM OF UNIT.
2. ALL DIMENSIONS ARE APPROX. IN INCHES [mm]
1. WEIGHT: 5500 LBS APPROX [2494.76 Kg]




PERMANENT LOAD BANK - THREE BAY UNIT
GENERAL REFERENCE OUTLINE DRAWING


Model 4830

1 OF 2

Rev. L



VIEW A-A



GROUND BUS BAR DETAIL
 GROUND BUS BARS IN EACH BAY
 GROUND BUS BARS ARE
 0.25 [6.35] THICK COPPER

