

ABL8MEM24012

PHASEO POWER SUPPLY 24VDC 1.2AMP



List Price \$141.00 USD

Availability **Stock Item: This item is normally stocked in our distribution facility.**

Technical Characteristics

| | |
|--------------------------|---------------------------------------|
| Description (Family) | Modular Power Supply |
| Marketing Trade Name | Phaseo® |
| Brand | Schneider Electric |
| Input Voltage | 100 to 240Vac |
| Output Voltage | 24Vdc |
| Phase | 1-Phase |
| Nominal Power | 30 W |
| Nominal Current | 1.2A |
| Mounting | DIN Rail / Panel |
| Wire Range | #14 to #26 AWG |
| Tightening Torque | 5.3 lb-in (0.6 Nm) |
| Description (Individual) | Power Supply 24Vdc 1.2 Amp |
| Certifications | UL Listed - CSA Certified - CE Marked |
| RoHS | Yes |
| Weight | 0.43 lbs (0.20kg) |

Shipping and Ordering

| | |
|-------------------|-------------------------------------------------------------------------|
| Category | 22525 - |
| Discount Schedule | CP12 |
| GTIN | 00785901551508 |
| Package Quantity | 1 |
| Weight | 0.51 lbs. |
| Availability Code | Stock Item: This item is normally stocked in our distribution facility. |
| Returnability | Y |
| Country of Origin | CN |

As standards, specifications, and designs change from time to time, please ask for confirmation of the information given in this document.