



Main

DIN EN 50083-1/A1, DIN EN 80083-2/A1

Broadband directional coupler box for branch-circuit and star-type distribution systems in broadband cable, communal aerial and satellite distribution systems. With DC transmission via the TV connection. Suitable for flush-mounted boxes of Ø 55-65 mm.

Complementary

With claw and screw fixing.

DC transmission: max. 24 V/400 mA

Signal: 22 kHz and DiSEqC

The information provided in this documentation contains general descriptions and/or technical characteristics of the performance of the products contained herein. This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications. It is the duty of any such user or integrator to perform the appropriate and complete risk analysis, evaluation and testing of the products with respect to the relevant specific application or use thereof. Neither Schneider Electric Industries SAS nor any of its affiliates or subsidiaries shall be responsible or liable for misuse of the information contained herein.