



IP54

Main

AC 230 V
Waterproof surface-mounted device with impact-resistant housing.
Reinforced relay.
High sensitivity to light.
Large wiring compartment.

Complementary

Connected load: up to 2300 VA
Max. switching current: AC 230 V, 10 A, $\cos\varphi = 0.6$
Halogen lamps: AC 230 V, up to 2000 W
Incandescent lamps: AC 230 V, up to 2300 W
Capacitive load: max. 140 μF
Connecting terminals: for 2.5 mm² rigid conductors
Adjustment range/switch threshold: 3 to 2000 lux, adjustable
Switching delay
- **when switching on:** approx. 40 s
- **when switching off:** approx. 100 s
Dimensions: approx. 97x80x47 mm

Accessories: Capacitor, art. no. MTN542895.

: without switching delay, light grey

The information provided in this documentation contains general descriptions and/or technical characteristics of the performance of the products contained herein. This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications. It is the duty of any such user or integrator to perform the appropriate and complete risk analysis, evaluation and testing of the products with respect to the relevant specific application or use thereof. Neither Schneider Electric Industries SAS nor any of its affiliates or subsidiaries shall be responsible or liable for misuse of the information contained herein.