



### Main

Using the U.motion Client Touch, it is possible to visualise and control the functions transferred from a U.motion KNX server.

### Complementary

These functions include:

- Control of the lighting, blinds and room temperature control, scenarios
- Visualisation of the energy efficiency
- In conjunction with a KNX Server Plus, communication within a building is possible (intercom, communication with the door station)
- Building monitoring using IP cameras

Operation is interactive on the touch-sensitive TFT display.

Suitable for flush-mounted installation, cavity wall installation and cavity wall installation in which the touch panel is flush-mounted with the wall. For horizontal installation.

**Nominal voltage:** AC 100 - 240 V

**Energy consumption:** max. 20 W

**Connections and interfaces:**

1 x LAN connection, Ethernet RJ45, 10/100/1000 Mbit/s

4x USB (1x front, 3x back)

**Display size:** 25.6 cm (10.1")

**Display type:** TFT, capacitive touchscreen

**Resolution:** WSVGA 1024x600

**Light intensity:** 200 cd/m<sup>2</sup>

**Contrast ratio:** 400:1

**Features:** Loudspeaker, microphone

**IP protection rating:** IP 20

**Dimensions:** 343x201x81 mm (LxHxW)

Contents: U.motion Touch 10 design elements. RJ45 connection adapter and Cat 6 patch cable 20 cm. U.motion USB stick with additional software and documentation.