



Main

Using the U.motion Client Touch, it is possible to visualise and control the functions transferred from a U.motion KNX server.

Complementary

These functions include:

- Control of the lighting, blinds and room temperature control, scenarios
- Visualisation of the energy efficiency
- In conjunction with a KNX Server Plus, communication within a building is possible (intercom, communication with the door station)
- Building monitoring using IP cameras

Operation is interactive on the touch-sensitive TFT display.

Suitable for flush-mounted installation, cavity wall installation and cavity wall installation in which the touch panel is flush-mounted with the wall. For horizontal installation.

Nominal voltage: AC 100 - 240 V

Energy consumption: max. 25 W

Connections and interfaces:

1 x LAN connection, Ethernet RJ45, 10/100/1000 Mbit/s

4x USB (2x front, 2x back)

Display size: 39.6 cm (15.6")

Display type: TFT, capacitive touchscreen

Resolution: WXGA 1366x786

Light intensity: 300 cd/m²

Contrast ratio: 500:1

Features: Loudspeaker, microphone

IP protection rating: IP 20

Dimensions: 525x306x92 mm (LxHxW)

Contents: U.motion Touch 15 design elements RJ45 connection adapter and Cat 6 patch cable 20 cm. U.motion USB stick with additional software and documentation.