


L5112D Range 12 Channel Professional Dimmers

C-Bus®

CLIPSAL®
LIVING ELECTRICAL



The C-Bus L5112D range of Professional dimmers are high powered 12 channel dimmers designed for commercial applications such as hotels, restaurants and office buildings.

The dimmers are C-Bus controlled, high power, multi phase control units, compatible with a wide range of load types, including neon.

Dimming is achieved through phase control techniques creating a highly efficient range of dimmers.

Channel derating for use with electronic transformer loads is not required. Each channel is capable of supporting full load current.

The L5112D range of Professional dimmers provides on-board MCB protection, thermal overload protection and also accommodates the RCD requirements as per AS/NZS3000:2007.

The dimmers contain modular output channel cards of various ratings, allowing customisation to suit site needs.

A maintained active output is provided on each channel for emergency lighting.

Each channel card has a bypass switch which permits direct local override of the lighting circuit.

In the event of an over-temperature condition, such as one caused by excessive load current being drawn, the dimmer channel reduces the output power as long as the condition exists.

The Professional dimmer is designed and tested for a wide range of international markets with comprehensive EMC and electrical safety testing and is fully ROHS compliant.

- Soft start load turn-on protects lamp filaments.
- Voltage compensation to minimise load brightness variation if the AC supply voltage drifts.
- Filtering reduces supply voltage signalling effects.
- Linear output load power following input control.

- C-Bus network burden and system clock generator.
- After mains fail, dimmers return to previous or preset values.
- Local C-Bus override switches on front panel.
- Channel Status indicators on front control panel.
- On-board MCB and optional RCD protection.
- Mounting brackets included for ease of installation.
- Generous load and mains supply terminals.
- Emergency lighting output for each channel.
- Manual dimmer bypass switch on all channels.
- Fan-free operation, reduces maintenance requirements.
- Suitable for single or three phase track lighting applications with optional three phase MCBs and RCDs
- Complies with Australian (AS/NZS CISPR 15:2002) and International standards for light dimmers as below.

Accreditations	C-Tick	CE
EMC	AS/NZS CISPR14-1 CISPR15	EMC Directive 2004/108/EC EN 60669-2-1 Clause 26.1, 26.2 EN 55014-1, 55015, 61000-3-2, 61000-3-3, 61000-3-5, 61000-3-11
Low Voltage		EN 60439-1, 60669-2-1
Electrical Safety	AS/NZS 3439-1 IEC 60669-2-1	IEC 60439-1, 60669-2-1
ROHS		2002/95/EC

clipsal.com/cis



L5112D Range 12 Channel Professional Dimmers

Catalogue Numbers

12 Channel	Leading Edge	Leading Edge + RCD*
20 A	L5112D20LP	L5112D20LPR12
16 A	L5112D16LP	L5112D16LPR12
10 A	L5112D10LP	L5112D10LPR6
5 A	L5112D5LP	L5112D5LPR6
3 A	L5112D3LP	

*20 A and 16 A RCD models include 12 × 2 pole RCBOs (Combination RCD and MCB)

*10 A and 5 A RCD models include 6 × 2 pole RCCBs (RCD Only, 2 channels / RCD)

*3 A model requires external RCD protection

Ratings

Catalogue Number	Max. Load Current/Phase
L5112D20LP	60 A, 3 Phase
L5112D16LP	60 A, 3 Phase
L5112D10LP	40 A, 3 Phase
L5112D5LP	20 A, 3 Phase
L5112D3LP	36 A, 1 Phase 18 A, 2 Phase

Electrical Specification

Parameter	Description
Load terminal standby leakage current	< 10 mA leading edge
AC supply voltage	240/415 V AC
AC supply frequency	47 to 53 Hz
Number of input phases	1 or 2 Phase (3 Amp model) 3 Phase (other models)
Minimum load/channel	20 W for incandescent
Dimming technology	Leading edge 3-5 A Triac Leading edge 10-20 A Dual SCR
Soft-start ramp time	0.5 sec
Load current rise time	200 µs
Power control range	1.5% to 95%
Standby AC supply current	90 mA base current 75 mA each LE Channel
Short circuit withstand strength	6 kA*
Rated insulation voltage	500 V
Dielectric test voltage	2500 V

*Note for 3 A model installer must connect dimmer to mains with protection rated at 20 A per phase 6 kA short circuit withstand strength

Dimensions

Catalogue	Weight (kg)	Dimensions W × H × D
L5112D20LP	40	455 × 713 × 164 mm
L5112D16LP	40	455 × 713 × 164 mm
L5112D10LP	31	412 × 713 × 164 mm
L5112D5LP	26	405 × 713 × 115 mm
L5112D3LP	23	405 × 602 × 115 mm

Product of Clipsal Australia Pty. Ltd.

A member of the Schneider Electric Group.

Head Office

12 Park Terrace, Bowden
South Australia 5007
PO Box 103 Hindmarsh
South Australia 5007

Telephone +61 8 8345 9500
Facsimile +61 8 8346 0845
Internet www.clipsal.com/cis
E-Mail cis@clipsal.com.au

CIS Technical Support Hotline:

1300 722 247

Customer Service Enquiries:

1300 2025 25

National Customer Service Facsimile:

1300 2025 56

International Enquiries

International Sales and Marketing

Telephone +61 8 8269 0587
Facsimile +61 8 8340 7350
E-Mail export@clipsal.com.au

New Zealand

Schneider Electric (NZ) Ltd
Telephone +64 9 576 3403

Malaysia

Clipsal Integrated Systems (M) Sdn Bhd
Telephone +60 3 7665 3555

Singapore

Clipsal Integrated Systems Pte Ltd
Telephone +65 6415 3232/3233

China

Clipsal China Limited
Telephone +86 755 8237 5959

Greece

Schneider Electric AE
Telephone +30 69 4646 3200

Hong Kong

Clipsal Integrated Systems (HK) Limited
Telephone +852 2487 0261

India

Schneider Electric India Pvt Ltd
Telephone +91 11 5159 0000

Indonesia

PT Clipsal Graha Nusa
Telephone +62 21 630 6430

Korea

Clipsal Korea Co. Ltd
Telephone +82 549 5550

Pakistan

Clipsal Pakistan (Pvt) Ltd
Telephone +92 21 506 7278

Philippines

Clipsal Philippines Inc.
Telephone +632 683 0275-78

South Africa

Clipsal South Africa (Pty) Ltd
Telephone +27 11 314 5200

Taiwan

Clipsal (Taiwan) Co Ltd
Telephone +886 2 2558 3456

Thailand

Clipsal Thailand Ltd
Telephone +66 2 952 5338-42

United Arab Emirates

Clipsal Middle East
Telephone +971 6 5570 777

United Kingdom

Clipsal Integrated Systems
C/o Schneider Electric
Telephone +44 870 608 8 608

Vietnam

Clipsal - VTEC
Telephone +848 856 3002



Clipsal Australia Pty Ltd reserves the right to change specifications, modify designs and discontinue items without incurring obligation and whilst every effort is made to ensure that descriptions, specifications and other information in this document are correct, no warranty is given in respect thereof and the company shall not be liable for any error therein.

© Clipsal Australia Pty Ltd.

The identified trademarks and copyrights are the property of Clipsal Australia Pty Ltd unless otherwise noted.