



Acer	Aspire 1300, 1310, 1680, 2000, AOPEN S1	19	K / k
	Aspire 5670 Ferrari 4000 Travelmate 230, 233, 234, 280, 281, 283, 290, 432, 433, 653, 660, 661, 662, 800, 802, 803, 2410, 4060, 4100, 4200, 4650, 4670, 6000, 8000, 8200, C200, C300, C301, C302, C303, C310	19	A / a
	Travelmate C100, C110	20	A / a
	Aspire 1400, 1640, 1691WLMi, 3000, 3502WLCi, 3610, 5000 Travelmate 420, 430, 4650, 8100	19	B / b
Apple	iBook G3 (Dual USB, 500 MHz & up), G4 PowerBook G4 (Titanium & Aluminum)	20	P / p
Averatec	1000 Series, 3150, C3500 Series	19	B / b
Compaq™	Presario 305, 306, 2800-2880	19	H / h
	Presario 700-955, 1010-1080, 1200-1280, 1450, 1600-1830, 2700-2720, 3045US, V2403NR	19	B / b
	Presario M2401XT, V2309US, V2310, V2335, V2402, V2404US, V2405, V2410US, V2413, V2414NR, V2424NR, V2552, V2555US, V2565US, V2570NR, V2575US, V2582US, V2606CU, V2615US, V2630US, V2658US, V2665US, V4135US, V4240US, V4332US, V4440US, V5005US, V5015US, V5101US, V5102NR, V5105US, V5108CU, V5115US, V5119US, V5120NR	19	K / k
Dell™	Inspiron 300M, 500M, 510M, 600M, 640M, 700M, 710M, 1150, 6000 Latitude D400, D410, D420, D500, D505, D510, D520, D600, D610, D620, D800, D810, X1, X200, X300 Precision M20	19	I / i
	Inspiron 1300, 2100, 2200, 3000-3500 Series, 7000	19	B / b
Fujitsu	Lifebook A1010, C2210, C2220, E4010, E4010D, E7010, E7110	19	B / b
	Lifebook A4170, C2010, E2010, E7000 Celsius Mobile H	19	E / e
	Lifebook 200-900 Series, B112-B2630, B3000D, B3010D, P1032-P2120, P5000, P5010, P5020, S2000, S2010, S2020, S4510-S6110, S6120, S6120D, S7000, S7010, T3000, T3000D, T3010 Stylistic Tablet 1000-3500, LT Series, ST Series	16	E / e
	Lifebook N3500	19	K / k
Gateway™	400S, 400SP, 400SP Plus, M275R	19	A / a
	6023GP, 6252GP, CX2610, MX3560, MX6025, MX6124, MX6650, MX7515	19	B / b
	200S, 200X, 200XL, 400X, 400XL, 450X	19	E / e

Hewlett-Packard	Omnibook z13000 nr3600, nr3610 Omnibook 2100-4150, 500, 6000-7150, 900, xe2-xe4500 Pavilion dc4150us, dv1331se, dv1411se, dv1420us, dv4250us, dv4275nr, dv5040us, ze2315us, ze4000, ze4315, ze4325, ze4345, ze4355, ze4365, ze4401, ze4420, ze4430, ze5000, zv6131us, zv6233nr, zv6270us Pavilion dv1227, dv4000, ze2115us	19	H / h
		19	B / b
HP Compaq	nc4010, nc4200, nc6120, nc6220, nc6230, nc8230, nx5000, nx6110, tr3000	19	B / b
	nc4000, nc4200, nc6000, nc8000, nx7000, nx7010, TC1000, TC1100	19	H / h
	nx9005, nx9010, nx9020, nx9030, nw8000	20	H / h
Lenovo	ThinkPad 3000, R60, T60, X60 Series (without discrete graphics card)	19	M / m
	ThinkPad A Series, R Series, T Series, X Series (excluding R60, T60, X60)	16	B / b
Mitac	3025, 3025D, 3025F, 3025F / SXL, 386 / 16, 6020T	19	A / a
	5013, 5026, 6020, 6031, 6120, 7020 Series	19	D / d
	4023, 4024, 5024	16	D / d
	MiniNote 7170, 7170P, 7321, 7521, 8080, 8100, 8170, 8175, 8375, 8575	19	B / b
Panasonic	Toughbook 18, 28, 29, 50, 73, R1, T1, T2, Y2	16	B / b
Sony	VAIO PCG-TR, PCG-V505, PCG-X505, PCG-Z1, V505A, V505B, VGN-3, VGN-T350PL, VGN-TX650PB, VGN-TX750PB	16	E / e
	VAIO PCG-700, PCG-800, PCG-900, PCG-F, PCG-FX, PCG-FXA, PCG-R505, PCG-XG, PCG-XR9, PCG-Z505, VGN-A, VGN-AX, VGN-FE, VGN-FJ, VGN-FS, VGN-S, VGN-SZ	19	E / e
Toshiba	Satellite A75-S1253, A80, A85, A100, A105 (except A105-S4xxx), L10, L15, L20, L25, M30X, M35X, M40-S312TD, M45-S165, M45-S165X, M45-S169, M55-S139, M55-S139X, M55-S141, M55-S1001, M65-S809, M65-S9062, M65-S9092, M105-S10xx Tecra L2	19	B / b
	Libretto S400, U105 Portege 300-660, 2000-2010, 3000-3490, 3500, 3505, 4000-7200, M100, M200, M205, M400, M405, R100, R200, R205-S2062, R205-S209, S100, S105-S1133, T3400 Satellite 5205-S705, A10, A10-S127, A10-S128, A10-S177, A10-S178, A15-S127, A15-S157, M30, M45-S265, M45-S269, M45-S355, M45-S359, M55-S135, M55-S325, M55-S3293, M105-S1xxx, M105-S3xxx, P100-S7xxx, P105-S6xxx, R15-S822, R15-S829, R20, R25, S100-S1133, U200, U205 Satellite Pro 6100 (1.8 & 2.2 GHz), M10-S405, M15-S406 Tecra A5-S516, A6, A7, A8, M1, M3, M4, M5, M6, M7, S1, S3	15	D / d

▶ Output voltage ratings can be found on your notebook computer's system label or power adapter label.

▶ For additional questions about compatibility, please visit : mobilecomputing.apc.com or call 800.800.4APC.